

Wireless Watcher Mini

(Model: WM44)

2.7kg lightweight camera

Transmission distance up to 120m

*Depending on environment usag

Video delay 100ms

(*Best effort measurements)

Use of camera power supply

External battery included

Full HD video

Up to 8x digital zoom

(Pinch-zoom/controller not required)

Lens is Facing down due to camera weight

Built-in Balancer function

Night mode allows work to perform well at night

WDR (Wide Dynamic Range)
Built-in function

Stabilizer (Image stabilization)

Built-in function

Simple installation using one bolt

The monitor is battery-powered and portable

(*Optional battery is available separately)

Integrated receiver monitor

Camera body (WM44-CAM)

(WM44-SHD)

Main Specifications

Camera part (WM44-CAM)

Transmission method Transmission distance	Wireless up to 120 m * Depending on usage environment	Radio frequency band	5.6 GHz (both video and operation) * Channel width is 20MHz
Camera power supply	Crane power supply(DC24V) can be obtained from battery or boom top	Number of channels Available	10 channels * Only 1 channel is used
Image element	1/2.8 CMOS Sensor	Video delay	100 ms
Effective pixels	About 2 million pixels		*There maybe some errors depending on the usage environment.
Lens	Digital 8x zoom lens (equipped with image stabilization function)	Continuous operating time	About 10 hours for battery
Horizontal angle view	52.7°	Dimensions	(W)110 mm× (D) 87 mm x (H) 150 mm ※ Excluding balancer
Minimum subject illuminance	0.001 lx		
Environmental resistance	IP67	Weight	About 2.7 kg (Excluding battery)

Integrated Receiver Monitor (WM44-SHD)

Screen	7 inch IPS LCD		
Resolution	1920×1200		
Maximum brightness	1800 Nits		
Operating temperature	0 deg C ∼ 50 deg C		
Storage temperature	- 17.8 deg C ∼ 48.9 deg C		
Power-supply voltage	DC10V~34V		
Dimensios	(W)180 mm x (D) 30 mm x (H) 120 mm		

Component parts





Camera battery (battery case / battery body/charger)



Monitor battery (batterybody/charger) **Optional items



Monitor handle + neck strap

 $\ensuremath{\,\%\,} Optional\ items$



In order to use the product safely, please be sure to read the "Instruction Manual" carefully before use and use it correctly.

The quality test is conducted under a specific environment based on our standards, so we do not guarantee that the product will not be damaged or malfunction. Product ratings and designs are subject to change without notice for improvement. The color of this catalog and the actual product may differ slightly.





